V-INFINITY
a division of CUI INC

PART NUMBER: VABD6 **DESCRIPTION:** dc-dc converter

features
- **5-6 W isolated output**
- **efficiency to 82%**
- **2:1 input range**
- **regulated outputs**
- **Pi input filter**
- **24-Pin DIP package**
- **meets EN55022 Class B, conducted**
- **remote ON/OFF option**

RoHS

Discontinued

model number	input voltage	output voltage	output current	input current no load	input current full load	efficiency
VABD6-D12-S3R3	9-18VDC	3.3VDC	1000mA	7.5mA	393mA	70%
VABD6-D12-S5	9-18VDC	5VDC	1000mA	7.5mA	545mA	76%
VABD6-D12-S12	9-18VDC	12VDC	470mA	7.5mA	585mA	80%
VABD6-D12-S15	9-18VDC	15VDC	400mA	7.5mA	625mA	80%
VABD6-D12-D12	9-18VDC	±12VDC	±230mA	12mA	575mA	80%
VABD6-D12-D15	9-18VDC	±15VDC	±190mA	12mA	590mA	80%
VABD6-D12-D5	9-18VDC	±5VDC	±500mA	12mA	545mA	76%
VABD6-D24-S3R3	18-36VDC	3.3VDC	1000mA	5mA	197mA	70%
VABD6-D24-S5	18-36VDC	5VDC	1000mA	5mA	265mA	78%
VABD6-D24-S12	18-36VDC	12VDC	470mA	5mA	285mA	82%
VABD6-D24-S15	18-36VDC	15VDC	400mA	5mA	305mA	82%
VABD6-D24-D12	18-36VDC	±12VDC	±230mA	7.5mA	285mA	81%
VABD6-D24-D15	18-36VDC	±15VDC	±190mA	7.5mA	295mA	81%
VABD6-D24-D5	18-36VDC	±5VDC	±500mA	7.5mA	265mA	78%
VABD6-D48-S3R3	36-72VDC	3.3VDC	1000mA	2mA	98mA	70%
VABD6-D48-S5	36-72VDC	5VDC	1000mA	2mA	133mA	78%
VABD6-D48-S12	36-72VDC	12VDC	470mA	2mA	145mA	81%
VABD6-D48-S15	36-72VDC	15VDC	400mA	2mA	154mA	81%
VABD6-D48-D12	36-72VDC	±12VDC	±230mA	3mA	142mA	81%
VABD6-D48-D15	36-72VDC	±15VDC	±190mA	3mA	147mA	81%
VABD6-D48-D5	36-72VDC	±5VDC	±500mA	3mA	133mA	78%

NOTES:
1. suffix “HM” for 1.5K Vdc isolation
2. suffix “H” for 3K Vdc isolation
3. suffix “-SMT” for SMT case style
4. suffix “-1” for on/off control option

PART NUMBER: VABD6 **DESCRIPTION:** dc-dc converter

INPUT

input voltage range		12V	9-18V
		24V	18-36
		48V	36-72
input filter			Pi type

OUTPUT

voltage accuracy			±2.0% max.
voltage balance (dual)			±1.0% max.
temperature coefficient			±0.05% / °C max.
ripple and noise, 20MHz BW		3.3V / 5V	100mV p-p max.
		12V / 15V	1% p-p max.
short circuit protection			continuous
line regulation	single/dual[1]		±0.5%
load regulation	single[2]		±0.5%
	dual[3]		±1.0%

GENERAL SPECIFICATIONS

efficiency	see table
isolation resistance	10^9 Ohms
switching frequency	100kHz min.
isolation resistance	10^9Ohms
operating temperature range	-25°C to +71°C
storage temperature	-40°C to +100°C
cooling	free air convection
EMI/RFI	conductive EMI meet EN55022 class B
dimensions	1.25x0.8x0.5 inches (31.8x20.3x12.7mm)

ISOLATION VOLTAGE

500 VDC min	standard models
1.5K VDC min	suffix “HM” models
3K VDC min[4]	suffix “H” models

CASE MATERIAL

standard models	non-conductive black plastic
suffix “M” models[5]	black coated copper with non-conductive base

Discontinued

NOTES:
1. measured from high line to low line
2. measured from full load to 10% load
3. measured from full load to 1/4 load
4. non-conductive black plastic only
5. suffix “-1” to the model number with remote on/off for “H”/”HM” versions only

PART NUMBER: VABD6 **DESCRIPTION:** dc-dc converter

DIMENSIONS (mm)



Discontinued

DERATING CURVE



PIN CONNECTIONS

500 VDC					1.5K & 3K VDC				
Pin	Single Output		Dual Output		Pin	Single Output		Dual Output	
	DIP	SMD	DIP	SMD		DIP	SMD	DIP	SMD
1,24	+V Input		+V Input		1,24	NP	NC	NP	NC
2,23	NC		-V Output		2,3	-V Input		-V Input	
3,22	NC		Common		4	NP	NC	NP	NC
4	NP	NC	NP	NC	5	NP/ Remote On/Off	NC/ Remote On/Off	NP/ Remote On/Off	NC/ Remote On/Off
5	NP	NC	NP	NC	9	NC		Common	
9	NP	NC	NP	NC	10,15	NC		NC	
10,15	-V Output		Common		11	NC		-V Output	
11,14	+V Output		+V Output		12,13	NP	NC	NP	NC
12,13	-V Input		-V Input		14	+V Output		+V Output	
16	NP	NC	NP	NC	16	-V Output		Common	
20	NP	NC	NP	NC	20,21	NP	NC	NP	NC
21	NP	NC	NP	NC	22,23	+V Input		+V Input	

*NP-NO PIN *NC-NO CONNECTION WITH PIN *Remote On/Off (Option)